

केन्द्रीय मुहर विभाग-2

हमारा संदर्भ : के.मू.वी.-2/16:16190

16 03 2018

विषय : आई एस 16190:2014 "कृषि वस्त्रादी-सिंचाई के लिए उच्च घनत्व पालिएथाइलीन (एच डी पी ई) लेमिनेटेड बुनी ले फ्लेट ट्यूब" की प्रारूप ग्रुपिंग दिशा निर्देश

1. आई एस 16190:2014 के प्रारूप ग्रुपिंग दिशा निर्देश तैयार की गई है एवं अवलोकन के लिए संलग्नित है ।
2. सभी संबंधित से अनुरोध हैं कि प्रारूप दस्तावेज की जांच करें और 23 मार्च 2018 तक केन्द्रीय मुहर विभाग-2 को टिप्पणी भेजें ।
3. सभी शाखा कार्यालयों से अनुरोध किया जाता है कि संबंधित प्रारूप दस्तावेज को सभी आवेदकों/ लाइसेंसधारियों को जो उनके अधिकार क्षेत्र में हैं, टिप्पणियों के लिए उनकी जानकारी में लाए और साथ ही टिप्पणियों को, यदि कोई हो, निर्धारित समय के भीतर केन्द्रीय मुहर विभाग-2 को भेजें ।

(आदित्य दास)
वैज्ञा.सी.

प्रमुख (CMD-2)

सभी क्षेत्रीय/शाखा/टीएक्सडी कार्यालयों को परिचालित

प्रतिलिपि: ITS इंटरनेट पर अपलोड करने के लिए

CENTRAL MARKS DEPARTMENT-2

Our Ref: CMD-2/16:16190

16 03 2018

Subject: Draft grouping guidelines for Agro Textiles – High Density Polyethylene (HDPE) Laminated Woven Lay Flat Tube for Irrigation Purpose as per IS 16190:2014

1. Draft grouping guidelines for IS 16190:2014 have been prepared and are enclosed for comments. BOs are requested to examine and provide their comments within **23 March 2018**.
2. All BOs are also requested to bring the draft document to the notice of applicants/licensees under their jurisdiction for their comments as well and forward such comments, if any to CMD-2 within the stipulated time as above.

(Aditya Das)
Scientist C

Head CMD-2

Circulated to: All ROs/BOs/TXD

Copy to: ITS – for hosting on BIS Website

DRAFT FOR COMMENTS

CENTRAL MARKS DEPARTMENT-2

Our Ref: CMD-2/16:16190

16 03 2018

Subject: Grouping Guidelines for “Agro Textiles – HPDE Laminated Woven Lay Flat Tube for Irrigation Purpose” as per IS 16190:2014

1. IS 16190:2014 covers the following 9 sizes of lay flat tubes:

Nominal Internal Diameter, mm: 50, 65, 75, 90, 110, 125, 150, 175, 200

2. Considering the above, the following grouping guidelines for grant of licence/inclusion of additional variety in the licence have been developed, classifying the lay flat tubes into following groups:
 - i. Group 1 – 50 to 75 mm
 - ii. Group 2 – 90 to 125 mm
 - iii. Group 3 – 150 to 200 mm
3. In order to cover all sizes in a particular group, one sample from each group shall be tested to cover all sizes in that group.
4. However, while considering grant of licence/inclusion of additional sizes/varieties, it shall be ensured that complete manufacturing and testing facility is available with manufacturer. During the operation of licence, BOs shall ensure that all sizes covered in the licence shall be tested in rotation, to the extent possible.
5. The above guidelines shall come into force with immediate effect.

Aditya Das
Scientist C

Head CMD-2
DDG (Certification)